






REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	ECN-0503095	2005/03/21	XLM	Ref. To ECN.Note



Note:

- 1.Cable Range:ø6.0~ø10.0mm
適用線徑:ø6.0~ø10.0mm
- 2.For Panel Thickness Max 7.5mm
適用板厚 :7.5mm
- 3. Color: Gray
顏色 : 灰色
- 4. @@ Important Dimension.
(@@ 為重點檢驗尺寸)

5	Sealing Nut	Gray	Nylon	1	ANC173XXX06
4	Seals	Black	EPDM	1	DGA0030EP70
3	Clamp Ring	Gray	Nylon	1	ANC350XXX06
2	Gasket	Black	EPDM	1	DGA0071EP70
1	Nut	Gray	Nylon	1	ANC292XXX06

ITEM NO	COLOR	SPECIFICATION	QTY	NOTE
---------	-------	---------------	-----	------

UNIT:mm	
TOLERANCE	±0.25 XX ±0.1 XXX ±0.05 ANGLES ±1°
SCALE	1/1
REV.	B
SIZE	A4
@@	inspection item

Amphenol LTM
安費諾亮泰企業股份有限公司

DWG NO	CSG-16M003	CHECKED BY	Wu Dong	DATE	2005/03/21
CUSTOMER	ALTW	APPROVED BY	Steven Chen	DATE	2005/03/21