



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14						
			P	REVISED PER ECO-14-015277	10FEB2015	NK	DR



- 1 TONGUE MATERIAL THK IS .018±.002.
2 MEETS MS25036-146, CLASS 2.

1	WIRE TERMINAL INSULATION RESTRICTING	BODY: COPPER (ASTM-B152) TIN PL (ASTM-B545) SLEEVE: COPPER (ASTM-B152) NICKEL PL. (QQ-N-290) INSULATION: NYLON COLOR: YELLOW (ASTM-D4066) TYPE 1	2-323916-3
100	LOOSE PC, BOX	BODY & SLEEVE: COPPER (ASTM-B152) TIN PL (ASTM-B545) INSULATION: NYLON COLOR: YELLOW (ASTM-D4066) TYPE 1	8-323916-1
4000	323916 ON TAPE		2 2-323916-1
1	WIRE TERMINAL		2 323916
QTY	DESCRIPTION	MATERIAL & FINISH	PART NO

8-323916-1	FIGURE 1	#26-#22	NONE	-	-
2-323916-3	FIGURE 2	#24	BLUE	.031/.055	-
323916 2	FIGURE 1	#26-#22	NONE	-	2-323916-1 2
PART NO.	STYLE	WIRE SIZE	STRIPE COLOR	"X/Y"	PART NO. ON TAPE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 02OCT09	TE Connectivity			
DIMENSIONS: INCHES		CHK TOM MICHIELUTTI 02OCT09				
		APVD MIKE PERCHERKE 02OCT09	NAME TERMINAL, NYLON - PIDG - RING TONGUE WIRE SIZE: 26-22			
		PRODUCT SPEC	-			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	-			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± 5°		WEIGHT	-			
FINISH		CUSTOMER DRAWING	SCALE 10:1 SHEET 1 of 1 REV P			
MATERIAL SEE TABLE		FINISH SEE TABLE		SIZE A2		
				CAGE CODE 00779		
				DRAWING NO 323916		
				RESTRICTED TO -		