

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , -



COPYRIGHT

By

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD



B4

REVISED (ECR-13-009702)

14MAR13


S.H

V.P






A-A

PLUG OVERMOLD



DC PLUG CONNECTOR
TE P/N: 1-2129334-1

MATING CONDITION



A'SSY P/N			
1-2129333-2	1-2129333-1	2129333-2	2129333-1
2	2	2	2
1	1	1	1
2	2	2	2
1			
	1		1
Q'TY			

0.0002mm GOLD PLATING ON CONTACT AREA, 0.002mm MATTE TIN PLATING ON SOLDER AREA, 0.002mm MIN. NICKEL UNDERPLATED ALL OVER

0.0002mm GOLD PLATING ON CONTACT AREA, 0.002mm MATTE TIN PLATING ON SOLDER AREA, 0.002mm MIN. NICKEL UNDERPLATED ALL OVER

0.0002mm GOLD PLATING ON CONTACT AREA, 0.002mm MATTE TIN PLATING ON SOLDER AREA, 0.002mm MIN. NICKEL UNDERPLATED ALL OVER

BLACK

YELLOW

FINISH/COLOR

COPPER ALLOY

POWER CONTACT

COPPER ALLOY

DETECT CONTACT

COPPER ALLOY

GROUND CONTACT

HIGH TEMPERATURE
THERMO-PLASTIC
(UL94V-0)

HOUSING

HOUSING

MATERIAL

PART NAME

NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 24FEB2012

CHK S.HUANG

APVD V.PENG

24FEB2012

W.KODAMA

24FEB2012

PRODUCT SPEC

108-99035


APPLICATION SPEC

501-99040

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:
mm



MATERIAL
SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0-PLC ±
1-PLC ±
2-PLC ±
3-PLC ±
4-PLC ±
ANGLES ±
FINISH

24FEB2012

S.HUANG

V.PENG

24FEB2012

W.KODAMA

24FEB2012

PRODUCT SPEC

108-99035

APPLICATION SPEC

501-99040

WEIGHT

CUSTOMER DRAWING



TE Connectivity

DC POWER JACK CONNECTOR
CABLE TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2129333

SCALE

4:1

SHEET



1 of 2

REV

B4

LOC	DIST	REVISIONS				
DW		P	LTR	DESCRIPTION	DATE	APVD
		—	—	SEE SHEET 1	—	—

DC POWER JACK CONNECTOR
TE P/N: 1-2129333-1/-2



- 1. EU ROHS-RELATED RESTRICTED SUBSTANCE SPEC IN HOMOGENEOUS MATERIAL REFER TO TEC-138-702 REV.G:
LEAD < 1000PPM, CADMIUM < 100PPM, MERCURY < 1000PPM
CHROMIUM VI < 1000PPM, PBB <1000PPM, PBDE < 1000PPM
- 2. HALOGEN FREE SPEC:
CHLORINE (Cl): 900 ppm MAX.
BROMINE (Br): 900 ppm MAX.
CHLORINE (Cl) + BROMINE (Br): 1500 ppm MAX.
- 3. SHIPPING BOX DIMENSION: 445mmX445mmX270mm

132	25	3300
PCS/TRAY	TRAY/SHIPPING BOX	TOTAL Q'TY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
DIMENSIONS: mm		CHK				
		APVD	NAME DC POWER JACK CONNECTOR CABLE TYPE			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — ±0.25 3 PLC ± — ±3 4 PLC ± — ANGLES ± —		PRODUCT SPEC				
MATERIAL		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
FINISH		WEIGHT	A3	00779	C-2129333	—
CUSTOMER DRAWING				SCALE	SHEET	REV
				NA	2 OF 2	B4