


PART NO.	BASE TYPE	DESIGN VOLTS	DESIGN AMPS	AVERAGE LIFE HOURS
LM1012MB	MINIATURE BAYONET	* 12 VDC	30-56mA	100,000

* BI-POLAR
OPERATIONAL VOLTAGE
10.8 - 13.2 VDC



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
1	ISSUED	01/21/2005	D.C.
2	OPERATIONAL VOLTAGE	06/23/2008	D.C.

COLOR	PART NUMBER	LUMEN
RED	LM1012MB-R	3.80
AMBER	LM1012MB-A	1.85
WHITE	LM1012MB-W	3.10
BLUE	LM1012MB-B	0.88
GREEN	LM1012MB-G	3.85
WARM WHITE	LM1012MB-WW	2.50

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES DECIMALS .XX ± .05 ANGULAR ± 0.5° .XXX ± .010 FRACTIONAL ± 1/64		CEC INDUSTRIES LTD	
		599 Bond Street	Lincolnshire IL 60069
DRAWN D. C.	DATE 01/21/2005	TITLE TRUE 360° LED MINIATURE BAYONET BASE LAMP 12 VOLT DC	
CHECKED		SIZE A	FSCM NO. LM1012MB REV 2
DESIGN		SCALE	PLOT SCALE SHEET 1 OF 1
MATERIAL		FILE LM1012MB.DWG	DO NOT SCALE DRAWING