




MARKING:



MARKING:



NOTE: INNER BODY IS BLUE



WIRING COLOR:

E: Yellow/Green
 N: Blue
 L: Brown

LENGTH ON CORD: (204-14)

SG1S <VDE> KEMA-KEUR <IEC 60335> <VDE> △ CENELEC 809
 NF-USE 1346 IEMMEQU H05VV-F 3G 0.75mm² 60227 IEC 53 RVV 306/500V
 A003083 3ASL/75 4V-75 V-75(75°C) 250/440V ORDINARY DUTY Q88228 -LF- CE

No	BOM ITEM	Q'TY	P/N
1	KPR-11 TERMINAL	3 pcs	BBN11000
2	IS-011 DUST COVER	1 pcs	MP0110HG
3	IS-011 INNER BODY	1 pcs	MI011000
4	PVC 45P (SA87, IS-011)	18 g	RPP045HG
5	KPR-14 TERMINAL	3 pcs	BBB14000
6	IS-14 INNER BODY	1 set	MI014000
7	PVC 45P (SA87, IS-14)	22 g	RPP045HG
8	PE TIE (WHITE · 6 inch)	1 pcs	KBW10006

CABLE H05VV-F 3G 0.75 DENT PRINT CT-HG (BLUE)						
PLUG	IS-011 + IS-14	LENGTH	1000	UNIT	mm	
CABLE	NAME	First connectivity	N/W	0.108343	UNIT	kg
	P/N	P-C14C13BLU1	SG DWG	SR-131723-3	VER.	A
				Design. by		
				Review. by		
				Approval. by		
X14 6B3016 HG 100 00						