





MARKING:

MARKING:



NOTE: INNER BODY IS RED



WIRING COLOR:

E: Yellow/Green
N: Blue
L: Brown

LENGTH ON CORD: (204-14)

SGS VDE KEMA-KEUR H05VV-F 3G 0.75mm² 60227 IEC 53 RVV 300/500V NF-USE 1346 IEMNEQU 3ASL/75 4V-75 Y-75(75°C) 250/440V ORDINARY DUTY Q88228 -LF-

No	BOM ITEM	Q' TY	P/N
1	KPR-11 TERMINAL	3 pcs	BBN11000
2	IS-011 DUST COVER	1 pcs	MP0110XF
3	IS-011 INNER BODY	1 pcs	M1011000
4	PVC 45P (SA87, IS-011)	18 g	RPP045XF
5	KPR-14 TERMINAL	3 pcs	BBB14000
6	IS-14 INNER BODY	1 set	M1014000
7	PVC 45P (SA87, IS-14)	22 g	RPP045XF
8	PE TIE (WHITE, 6 inch)	1 pcs	KBW10006

CABLE	H05VV-F 3G 0.75 DENT PRINT CT-XF (RED)				
PLUG	IS-011 + IS-14	LENGTH	500	UNIT	mm
NAME	First connectivity	N/W	0.074272	UNIT	kg
P/N	P-C14C13RED0.5	SG DWG	SR-131723-1	VER.	A

Design. by

Review. by

Approval. by

X14 6B3016 XF 050 00