




MARKING:



MARKING:



WIRING COLOR:

E: Yellow/Green

N: Blue

L: Brown

LENGTH ON CORD: (205-14)

<VDE> KEMA-KEUR 005 005 005 <VDE> △CEBEC 809 00000
 NF-USE 1346 IEMMEQU H05VV-F 3G 1.0mm² 60227 IEC 53 RVV 300/500V
 A003083 3ASL/100 4V-75 V-75(75°C) 250/440V ORDINARY DUTY Q90033 -LF- CE

No	BOM ITEM	Q' TY	P/N
1	KPR-11 TERMINAL	3 pcs	BBN11000
2	IS-011 DUST COVER	1 pcs	MP01101H
3	IS-011 INNER BODY	1 pcs	MI011000
4	PVC 45P (SA87, IS-011)	18 g	RPP0451H
5	KPR-14 TERMINAL	3 pcs	BBB14000
6	IS-14 INNER BODY	1 set	MI014000
7	PVC 45P (SA87, IS-14)	22 g	RPP0451H
8	PE TIE (WHITE, 8 inch)	1 pcs	KBW10008

NOTE:

IS-011 DUST COVER MUST USE "GRAY" COLOR COVER

CABLE		H05VV-F 3G 1.0 DENT PRINT CT-1H (GRAY)				
PLUG		IS-011 + IS-14	LENGTH	3000	UNIT	mm
CLIENT	NAME		N/W		UNIT	kg
	P/N	P-C14C13G3	SG DWG	SR-140085-27	VER.	A

X14 6C3016 1H 300 00