


MARKING:





MARKING:



No	BOM ITEM	Q' TY	P/N
1	97606-1 TERMINAL	2 pcs	BBN97606
2	97607-1 TERMINAL	1 pcs	BBN97607
3	IS-018 INNER BODY(YM-C20)	1 pcs	MP020S12
4	PVC 45P (SA87, IS-018)	30 g	RPP04505
5	98739PS-0 BLADE	3 pcs	BBP98739
6	IS-16 INNER BODY(YM-C19)	1 set	MI016S12
7	PVC 45P (SA87, IS-16B)	30 g	RPP04505
8	PE TIE (WHITE · X inch)	1 pcs	KBW1000X

NOTE: INNER BODY[CT-12 (BLACK)].



WIRING COLOR:

E: Yellow/Green
N: Blue
L: Brown

LENGED ON CORD: (206-14)

△VDE△ KEMA-KEUR 400 400 400 △VDE△ △ CEBC 809 000000
NF-USE 1346 IEMMEQU H05VV-F 3G 1.5mm² 60227 IEC 53 RYV 300/500V
A003083 3ASL/150 4V-75 V-75 (75°C) 250/440V ORDINARY DUTY Q96257 -LF- CE

CABLE	H05VV-F 3G 1.5 DENT PRINT CT-05 (Orange)				
PLUG	IS-018 + IS-16B	LENGTH	L1	UNIT	mm
NAME		N/W		UNIT	kg
P/N	P-C20C190X	SG DWG	SR-140085-30	VER.	A

X8B 6E3016 05 XXX 00