




MARKING:



MARKING:



WIRING COLOR:

E: Yellow/Green

N: Blue

L: Brown

LENDED ON CORD: (D5R33-SG)

NF-USE 1353 IENMEQU H05RR-F 3G 1.0mm<sup>2</sup> Q051568 CABO FLEX IVE IEC  
 60245-4 A041481 60245 IEC 53(YZ) 300/500V

No	BOM ITEM	Q' TY	P/N
1	SP-60 NICKEL INSERT	1 pcs	MB060001
2	FUSE 13A	1 pcs	KFC0013A
3	SP-60 FUSE COVER	1 pcs	MI0602RA
4	SP-60 INNER BODY COVER	1 pcs	MI0601RA
5	PVC 45P (SA87, SP60)	52 g	RPP04512
6	KPR-14 TERMINAL	3 pcs	BBB14000
7	IS-19 INNER BODY(YM-B7-00)	1 pcs	MI019000
8	IS-19 INNER BODY(YM-B7-10)	1 pcs	MI019001
9	PVC 45P (SA87, IS-19)	25 g	RPP04512
10	PE TIE (BLACK · 6 inch)	1 pcs	KBB10006
11	LABEL 13A	1 pcs	KLCA013A

CABLE H05RR-F 3G 1.0 CT-12 (BLACK)						
PLUG		SP-60 + IS-19(13A)	LENGTH	2000	UNIT	mm
CLIENT	NAME		N/W		UNIT	kg
	P/N	P-UK13C15B2	SG DWG	SR-132931-1	VER.	A

Y69 WC31SG 12 200 00