




MARKING:



MARKING:



WIRING COLOR:

N: Blue
L: Brown

LENGED ON CORD: (201-14)

◁VDE▷ KEMA-KEUR 400 VDE ▷ △ CEBEC 809 ⓈⓈⓈⓈ
 NF-USE 1346 IEMMEQU H03VVH2-F 2x0.75mm² 60227 IEC 52 RVV 300/300V Ⓢ
 A003083 2LDF/75 4V-75 V-75 (75°C) 250/250V LIGHT DUTY Q90096 -LF- Ⓢ

No	BOM ITEM	Q' TY	P/N
1	SAA118 INSULATION BLADE	2 pcs	BBN1181N
2	SP-501A INNER BODY	1 pcs	M1501A00
3	PVC 45P (SA87, SP-501A)	24 g	RPP04512
4	∅2.35B PHOSPHOR BRONZE TUBE	2 pcs	BPP235B3
5	IS-033 INNER BODY	1 pcs	M1333212
6	PVC 45P (SA87, IS-033)	9 g	RPP04512
7	PE TIE (BLACK, 6 inch)	1 pcs	KBB10006

CABLE H03VVH2-F 2x0.75 DENT PRINT CT-12 (BLACK)					
PLUG	SP-501A + IS-033	LENGTH	2000	UNIT	mm
CLIENT	NAME	N/W		UNIT	kg
	P/N	P-AUSC7B2	SG DWG	SR-140085-2	VER.

F13 7B2013 12 200 00