

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



\* UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMAL IS: X.X ±0.35 X.XX ±0.25

X.XXX ±0.15 ±1° X.X° ±0.05°





## **NOTES:**

## 1.CHARACTERISTICS:


- 1.1 RATED VOLTAGE:250V.
- 1.2 RATED CURRENT: 3AMP.
- CONTACT RESISTANCE: 35mohms MAX.INITAL. 50mohms MAX.AFTER.
- 1.4 INSULATION RESISTANCE:1000mohms MIN.at 500V DC.
- 1.5 DIELECTRIC STRENGTH :500VRMS .
- 1.6 OPERATING TEMPERATURE RANGE:-55°C~85°C.
- 1.7 INSERTION/EXTRACTION FORCE PER CONTACT:340g Max./21g Min.


## 2.MATERIAL:

- 2.1 INSULATORS:PBT+30% G.F(UL94V-0) BLACK.
- 2.2 CONTACTS:BRASS C2800R-H,(G/F")TOP OVER CONTACT AREA,100u" Min MATTE-TIN TOP OVER SOLDER AREA, 504"Min NICKEL UNDER PLATE.
- 2.3 FRONT SHELL:SPCC.100u" Min BRIGHT TIN TOP OVER.50u" Min COPPER UNDER PLATE.
- 2.4. BACK SHELL:SPCC.100u" Min BRIGHT TIN TOP OVER.50u"Min COPPER UNDER PLATE.

Ordering Info	Dimensions(mm)				
Part Number	SIZE	A±0.25	B±0.25	C±0.25	D± 0.25
MHDD09-M-T-B-S	9	30.81	24.99	16.33	19.28
MHDD15-M-T-B-S	15	39.25	33.32	24.66	27.75
MHDD25-M-T-B-S	25	53.03	47.04	38.38	41.25
MHDD37-M-T-B-S	37	69.40	63.50	54.85	57.40

	HE MANUFACTURE OR SALE OF APPARATUS WITHOUT					OVED
F	THESE DRAWINGS AND SPE PROPERTY OF MH CONNEC BE REPRODUCED, COPIED (	DRAW	HALE,			
	MHDD37-M-T-B-S	37	69.40	63.5	50	54.8
	MHDD25-M-T-B-S	25	53.03	47.0	)4	38.3
	MHDD13-M-1-B-3	13	39.23	33.0	)_	24.0





P.C.B LAYOUT



THIS SERIES FULLY CONFORMS TO THE **EUROPEAN UNION DIRECTIVES 2002/95/EC** AND 2002/96/EC FOR RoHS COMPLIANCY.



5.0±0.30

## MH CONNECTORS LTD.

WRITTEN PERMISSION.

SCALE	SHEET	OF	REV:
	1 🗆	IF 1	3.0
DD AVAUNO N			-

DATE

DATE

08-07-13

08-08-13

DRAWING No MHDDXX-M-T-B-S

DAMIEN