



data contact plating: Au 1.27µm (50pinch) over nickel

- for solid and stranded conductors AWG 27 up to AWG 22
- max. wire diameter 1.5mm
- cable diameter 4.9 - 8.6mm
- degree of protection IP65/IP67
- Cat.6 performance class EA suitable for 1/10 Gigabit ethernet
- temperature range -40°C up to +70°C
- 750 mating cycles

	All rights reserved Department EC PD - DE	All Dimensions in mm Original Size DIN A4		Scale 1.5:1	Free size tol.	Ref. Sub. TB 09 45 145 1560 / Mod. 36311 / 12.09.2011	
		Created by ZWAHR	Inspected by DAHMS	Standardisation HOFFMANN	Date 2016-02-24	State Final Release	
HARTING Electronics GmbH D-32339 Espelkamp		Title PushPull V4 RJ45 10G Cat6 plug 8pole IDC				Doc-Key / ECM-Nr. 100218635/UGD/001/B 500000100723	
		Type TB	Number 09451451560			Rev. B	Page 1/1