



2			1				
LOC	DIST	REVISIONS					
G	14	P	LTR	DESCRIPTION	DATE	DWN	APVD
			G2	REVISED PER ECO-16-001643	05FEB2016	NK	DR

AMP WIRE RANGE	 E13288 Listed
8 AWG SOLID OR STRANDED	8 AWG STRANDED
 LR7189 Certified	MILITARY P/N AND CLASS
8 AWG SOLID OR STRANDED	NOT APPLICABLE

- 1 STAMP AMP 8* 14 APPROX AS SHOWN
- 2 TIN PL 0.00254[.000100] MIN THK
PER ASTM B-545
- 3 NICKEL PL 0.00162[.000300] MIN THK
PER QQ-N-290
- 4 NOTE DELETED



OBSOLETE	50	LOOSE PIECE, BOX	-	8-35247-2
	1,000	MOUNTED ON TAPE, REEL	2 -	2-35247-2
	-	LOOSE PIECE	3 -	2-35247-1
	-	LOOSE PIECE	2 -	35247
	QTY	PACKAGE TYPE	FINISH	TE PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 22AUG97	 TE Connectivity			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	RECOMMENDED OPERATING TEMPERATURE: 170° C MAX	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK MJ SPICER 22AUG97				
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: NOT APPLICABLE		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD JL MECKLEY 22AUG97	NAME			
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE: 6.64-10.50mm ² [13,100-20,800] CIR MILS SOLID OR STRANDED		FINISH	PRODUCT SPEC	TERMINAL, RING TONGUE, SOLISTRAND™			
			MATERIAL COPPER PER ASTM B-152 ANNEALED	SEE TABLE	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
						WEIGHT	A300779		C-35247
						CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1
								REV G2	