


RECOMMENDED PANEL TOLERANCE ± 0.10
THICKNESS 1.15 ± 0.10

NOTES:

1. MATERIALS: POLYESTER, UL 94V-0, BLACK
2. PRODUCT SPECIFICATION: PS-151014-0001
3. USE FEMALE CRIMP TERMINAL: 50394-8***
4. APPLICABLE WIRE RANGE: AWG#24-#30
5. PACKAGING: BULK , PK-151014-0001
6. MATES WITH: 151013 SERIES
7. WHEN THIS PRODUCT IS USED AS A BLIND MATING APPLICATION THE SYSTEM LEVEL DESIGN MUST INCORPORATE GUIDANCE SO THE CONNECTORS ARE WITHIN THE CAPTURE ENVELOPE OF THE FLANGES ON THE HEADER OR PLUG HOUSING AND CAN THUS ALIGN THEMSELVES AS THEY COME TOGETHER
8. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPEC PS-45499-002
9. USE TOOL NUMBER 63813-1400 TO REMOVE TERMINAL FROM HOUSING WHEN NECESSARY
CAUTION: TERMINALS MUST NOT BE REUSED AFTER REMOVAL.
10. MOLEX LOGO AND CAVITY ID TO BE LOCATED APPROXIMATELY AT SHOWN
11. NON FUNCTIONAL CORING IS SUBJECTED TO CHANGES WITHOUT NOTICE



<div>P/N UPDATES</div> <div>EC NO: S2016-0689</div> <div>2015/12/04</div> <div>DRWNEANG</div> <div>2016/02/11</div> <div>CHKD:CGOH</div> <div>2016/02/11</div> <div>APPR:KHLIM</div>	<div>DESCRIPTION</div>	<div>QUALITY SYMBOLS</div> <div>F_A=0</div> <div>F_G=0</div> <div>F_P=0</div>	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	<div>THIRD ANGLE PROJECTION</div>
					MM ONLY		NTS	METRIC	
					DRAWN BY DATE		TITLE		
					CHECKED BY DATE		2MM PITCH		
					APPROVED BY DATE		CRIMP RECEPTACLE HOUSING WITH PANEL MOUNT FEATURE		
2	<div>REV</div>		ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.
			DRAFT WHERE APPLICABLE		1510140008		SD-151014-0001		1 OF 1
			MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		