






RECOMMENDED PCB LAYOUT
FOR USE WITH 0.20 [.008] THICK STENCIL

		—	30.48 [1.200]	14	32.61 [1.284]	30	6-147279-4
		—	30.48 [1.200]	13	32.61 [1.284]	28	6-147279-3
		—	30.48 [1.200]	10	32.61 [1.284]	22	6-147279-2
		—	30.48 [1.200]	8	32.61 [1.284]	18	6-147279-1
		44mm	30.48 [1.200]	12	32.61 [1.284]	26	6-147279-0
		44mm	17.78 [.700]	7	19.91 [.784]	16	5-147279-9
		24mm	12.7 [.500]	5	14.83 [.584]	12	5-147279-8
		24mm	7.62 [.300]	3	9.75 [.384]	8	5-147279-7
		44mm	27.94 [1.100]	11	30.07 [1.184]	24	5-147279-6
		44mm	22.86 [.900]	9	24.99 [.984]	20	5-147279-5
		24mm	2.54 [.100]	1	4.67 [.184]	4	5-147279-4
		32mm	15.24 [.600]	6	16.46 [.684]	14	5-147279-3
		24mm	10.16 [.400]	4	12.29 [.484]	10	5-147279-2
		24mm	5.08 [.200]	2	7.21 [.284]	6	5-147279-1
		24mm	5.08 [.200]	2	7.21 [.284]	6	1-147279-1
		44mm	30.48 [1.200]	12	32.61 [1.284]	26	1-147279-0
		44mm	17.78 [.700]	7	19.91 [.784]	16	147279-9
		24mm	12.7 [.500]	5	14.83 [.584]	12	147279-8
		24mm	7.62 [.300]	3	9.75 [.384]	8	147279-7
		44mm	27.94 [1.100]	11	30.07 [1.184]	24	147279-6
		44mm	22.86 [.900]	9	24.99 [.984]	20	147279-5
		24mm	2.54 [.100]	1	4.67 [.184]	4	147279-4
		32mm	15.24 [.600]	6	16.46 [.684]	14	147279-3
		24mm	10.16 [.400]	4	12.29 [.484]	10	147279-2
		24mm	5.08 [.200]	2	7.21 [.284]	6	147279-1
	PLATING	TAPE WIDTH	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER	10JUL00		 TE Connectivity		
		CHK J. GESFORD	10JUL00				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13 [.005] 4 PLC ± ± - ANGLES		APVD J. GESFORD		10JUL00	
		PRODUCT SPEC		NAME SURF. MT. HDR. ASSY, MOD II, B/W, VERT, D/R, .100 x .100 C/L .025 SQ POST, W/ PICK AND PLACE CAP			
		APPLICATION SPEC					
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		SEE TABLE		A2	00779	C-147279	-
CUSTOMER DRAWING				SCALE	4:1	SHEET	1 of 1
						REV	R1