




D





- 1 MATERIAL: CONTACTS - BRASS
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
HOLDDOWNS: - PHOSPHOR BRONZE.
- 2 PLATING: CONTACTS- 2.54µm MINIMUM TIN LEAD OVER 1.27µm MINIMUM NICKEL.
HOLDDOWNS- 2.54µm MINIMUM TIN-LEAD OVER 1.27µm MINIMUM NICKEL.
- 4 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 5 PLATING: CONTACTS-2.54µm MINIMUM TIN OVER 1.27µm MINIMUM NICKEL.
HOLDDOWNS- 2.54µm MINIMUM TIN OVER 1.27µm MINIMUM NICKEL.

C




B



A

PCB LAYOUT COMPONENT SIDE 4



5	33.00	40.27	40.00	12	3-1445057-2
5	30.00	37.27	37.00	11	3-1445057-1
5	27.00	34.27	34.00	10	3-1445057-0
5	24.00	31.27	31.00	9	2-1445057-9
5	21.00	28.27	28.00	8	2-1445057-8
5	18.00	25.27	25.00	7	2-1445057-7
5	15.00	22.27	22.00	6	2-1445057-6
5	12.00	19.27	19.00	5	2-1445057-5
5	9.00	16.27	16.00	4	2-1445057-4
5	6.00	13.27	13.00	3	2-1445057-3
5	3.00	10.27	10.00	2	2-1445057-2
2	33.00	40.27	40.00	12	1-1445057-2
2	30.00	37.27	37.00	11	1-1445057-1
2	27.00	34.27	34.00	10	1-1445057-0
2	24.00	31.27	31.00	9	1445057-9
2	21.00	28.27	28.00	8	1445057-8
2	18.00	25.27	25.00	7	1445057-7
2	15.00	22.27	22.00	6	1445057-6
2	12.00	19.27	19.00	5	1445057-5
2	9.00	16.27	16.00	4	1445057-4
2	6.00	13.27	13.00	3	1445057-3
2	3.00	10.27	10.00	2	1445057-2
FINISH	DIM Z	DIM V	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±0.13

3 PLC ±

4 PLC ±

ANGLES ±

FINISH

SEE TABLE

DWN J. ROOT 03-OCT-2000

CHK K. WHITAKER 13-MAR-2001

APVD K. WHITAKER 13-MAR-2001

PRODUCT SPEC 108-1836

APPLICATION SPEC 114-13000

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME

RT ANGLE SURFACE MOUNT HEADER ASSY, TIN CONTACTS W/SURF MOUNT HOLDDOWNS, SINGLE ROW, MICRO MATE-N-LOK TM

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-1445057

-

-

SCALE

5:1

SHEET

1

OF

1

REV

C2