




used for:

NOTES:

- 1, Current rating:10Amp AC300V
- 2, Insulation Withstands Voltage:
AC1500V/MIN
- 3, Insulation Resistance:
>1000M? DC500V
- 4, Operation temperature:
-40? C/+105? C



??						??		??	??	△	??		∕	≡	—	□	//												
2	8	16	24	32	0.5	3	6	30	120	0.5	3	6	10	50	120	all	all	5	30	120									
to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to									
8	16	24	32	38	3	6	30	120	480	3	6	30	10	50	120	400		5	30	120									
0.08	0.13	0.18	0.23	0.28	0.1	0.1	0.2	0.3	0.6	0.2	0.6	±1°	30'	20'	10'	0.2	0.5	0.025	0.06	0.13	0.4								
8												7												6					

△	初版		
REV.	CONTENT	CHK.	DATE

2	PIN	0037M00100	p	HPb59-1	Tin-Plated
1	HOUSING	0021P00000	1	PA66	UL94V-0
ITEM	NAME OF PART	NO OF PART	Q"TY	MATERIAL	NOTE
DWG.	ER	2004/05/17	UNITS	MM	SHEET/OF 1\1
CHK.	DATE		SCALE	1:1	
APP.	DATE				
				NAME	20.130M/XXP
				DWG NO.	

