Snaps and Pres-N-Snap Tool

Snaps are used to connect a ground cord to a static mat. Grommet and Clinch Style snaps are attached with a Pres-N-Snap. nickel plated brass snaps provide electrical connection and a long service life.



SNAPSOCKET3/8:

• 3/8" (10 mm) Female Snap Grommet Style

Socket snaps are held in place by crimping the tip of an eyelet though the center of the socket with a snap tool. This traps the mat between the socket on the top of the mat and the eyelet on the back of the mat. 10 sockets and eyelets are included in each pack.

SNAPSOCKET3/8

and 3034

Item

3033

3034

3050

FPSNAP

PRES-N-SNAP TOOL

SNAPSOCKET3/8

SNAPSTUD10 3/8

SNAPSTUD10 3/8:

• 3/8" (10 mm) Male Snap Grommet Style



Stud snaps are held in place by crimping the tip of an eyelet though the center of the stud with a snap tool. This traps the mat between the stud on the top of the mat and the eyelet on the back of the mat. 10 studs and eyelets are included in each pack.

FPSNAP:


• 3/8" (10 mm) Female Snap Prong Clinch Style

Prong Clinch snaps are held in place by pushing the prongs through the mat and crimping them on the bottom of the mat.

PRES-N-SNAP TOOL:

- For Attaching Grommet Style Snaps
- Versatile and easy to use.
- Capable of setting numerous brands of fasteners simply by changing the dies.





Description

3/8" Male Stud and Eyelet

3/8" Female 8-Prong Snap

3/8" Female Prong Snap

Snap Attaching Tool

3/8" Female Socket

3/8" Male Stud

3/8" Female Socket and Eyelet

Pres-N-Snap Tool Instructions

1. Press the eyelet through the mat from the back. (A utility knife or phillips screw driver can be used to make a hole.)

2. Place the socket or stud on top of the eyelet

Specifications and procedures subject to change without notice.

SNAPS AND PRES-N-SNAP TOOL

926 JR Industrial Drive, Sanford, NC 27332 WEB SITE: <u>StaticControl.com</u> PHONE (919) 718-0000

IBER	DATE
 N-SNAP	August 2015



FPSNAP and 3050

