

5



4

3

2

1



F



MOUNTING HOLE DETAIL


E

D



C

B



A

GENERAL TOLERANCES

10 UNDER	±0.2
10 OVER 30 UNDER	±0.25
30 OVER	±0.3
ANGLE	±3°

	5025-02P1	NO
	5025-02P	YES
EDP NO.	ENG. NO.	MTG. EAR

				公差 (Tolerances)	所要数	DRWG. 9/17/77
				.000 → ±0.005 .00 → ±0.05	(Req)	DSN'D H.8/1/77
				.0 → ±0.1 . → ±0.3		CHK'D 12/1/77
				材料 (MAT'L)		APP'D
				NYLON 66, 94V-2		
				熱処理 (H.T.)		
				HRc		
				仕上げ (Finish)		
D	ADDED -02P1 ECU NO. 917	9/17/77	1/2			
C	REMOVED "X" ECU NO. 748	9/17/77	1/2			
B	リブ、パネルスロット、エスケッチ No.	12/1/77	1/2			
A	REVISED	10/1/77	1/2			
O	PROPOSED	9/17/77	1/2			
記号 (LTR)	変更内容 (Rev.)	Date	Name	Scale 2/1	名称 (Name)	
					MINI. FIT CONN. 2POS. PLUG HSG.	

MOLEX-JAPAN CO., LTD.
日本モレックス株式会社

No. SD-5025-02P* REV. D

F



E

D

C




B

A



パネル板厚 2mm MAX

パネルスロット寸法



一般公差

10未満	±0.2
10以上30未満	±0.25
30以上	±0.3
角度	±3°

15-31-1023	5025-02P1	無
15-31-1021	5025-02P	有
EDP NO.	ENG. NO.	MTG. EAR

公差 (Tolerances)				所要数 (Req)		DRWG. <i>G. Awano 7/7/77</i>	
.000 → ±0.005 .00 → ±0.05				★		DSN'D <i>M. ENO 10/12/77</i>	
.0 → ±0.1 . → ±0.3						CHK'D <i>K. S. Ito</i>	
材料 (MAT'L)				MOLEX-JAPAN CO., LTD.		REV.	
NYLON 66, 94V-2				日本モレックス株式会社		E	
熱処理 (H.T.)				No. SD-5025-02P *			
HRc				仕上げ (Finish)			
E REVISED ECN NO. 1499 1/30/79 K.H.				Scale 2/1		名称 (Name)	
D ADDED -02P1 ECN NO. 917 7/5/78 4				MINI. FIT CONN. 2POS. PLUG HSG.			
C REMOVED "X" ECN NO. 748 3/18/78 4 VS							
B リブ, パネルスロット, サキット No. 12/16/77 142							
A REVISED 10/28/77 142							
O PROPOSED 7/7/77 142							
記号 (LTR)		変更内容 (Rev.)		Date		Name	