




NOTES: UNLESS OTHERWISE SPECIFIED
1. DIMENSIONS ARE IN INCHES
[mm]
2. ALL DEVICES U.L. LISTED & C.S.A CERTIFIED.
3. TERMINALS ACCOMODATE #14-10 AWG COPPER WIRE ONLY.

CATALOG NUMBERS								
BROWN	IVORY	GRAY	WHITE	BLACK	RED	ALMOND	CONFIGURATION	RATING
HBL5252	HBL5252I	HBL5252GY	HBL5252W	HBL5252BK	HBL5252R	HBL5252AL		15A-125V
HBL5352	HBL5352I	HBL5352GY	HBL5352W	HBL5352BK	HBL5352R	HBL5352AL		20A-125V

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
TOP	NYLON	
BASE	THERMOPLASTIC POLYESTER PHOSPHOR BRONZE	BLACK
CONT. SP. BIND. PLATE		
GR. CONTACT SP.	.031 BRASS	
WIRE CLAMP	.062 C.R.S.	NICKEL PL.
BRIDGE	BRASS	
GROUND SPRING	ST. STEEL	
BINDING SCREWS	BRASS	*
HEX. HD. BIND. SC.	BRASS	GREEN
MOUNTING SCREW	STEEL	ZINC PL.
WASHER	FIBER	RED
CENTER RIVET	SIL. BRONZE	

* = WHITE FINISH ON NEUTRAL PARTS WHEN USED

7	REMOVED "X" FROM RIVET; RIVET MATERIAL WAS BRASS PER DCN 16974 RCM	PJB PJB	10/20/10
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
3 WIRE GROUNDING STRAIGHT BLADE DUPLEX RECEPTACLE SIDE & BACK WIRED

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS $\pm 1/64$ DECIMALS $\pm .005$ ANGLES $\pm 2^\circ$	WIRING DEVICE--KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
	DR. BY ASM	APP. BY
	TR. BY	SCALE 1:1
	CHK'D BY	DATE 11/3/82