


M-7909 5



Ø 2.88
[73.2]

2.09
[53.1]

Ø 2.04
[51.8]

.13
[3.3]

CAT NO. & RATING
PRINTED ON FLANGE
COLOR CODE BY
VOLTAGE

TERMINALS WILL ACCEPT
16AWG TO 8AWG WIRE

LEGEND:
IN.
[mm]

NEMA NO.	RATING	POLE/WIRE	CAT NO.	CONFIGURATION	VOLTAGE COLOR CODE
L5-20R	125V	2P/3W GROUNDING	HBL2316		YELLOW
L6-20R	250V	2P/3W GROUNDING	HBL2326		BLUE
L7-20R	277VAC	2P/3W GROUNDING	HBL2336		GRAY
L8-20R	480VAC	2P/3W GROUNDING	HBL2346		RED
L9-20R	600VAC	2P/3W GROUNDING	HBL2356		BLACK
L24-20R	347VAC	2P/3W GROUNDING	HBL3726		BLACK

NOTE:
ALL SCREWS ARE COMBINATION PHILLIPS/SLOTTED/ROBERTSON HEAD.

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
CASING	NYLON	NATURAL
CONTACT BODY	NYLON	NATURAL
RETAINER	POLY CARBONATE	CLEAR
CONTACTS	.031 BRASS	
WIRE CLAMP	.080 CRS	NICKEL PLATE
#10 TERMINAL SCREWS	BRASS	*
#10 GROUND SCREW	BRASS	GREEN
ASSEMBLY FASTENERS	STEEL	ZINC PLATE
#8 MOUNTING SCREWS	BRASS	NICKEL PLATE

* WHITE FINISH ON NEUTRAL CONTACT WHEN USED

5	ADDED "CONFIGURATION" COLUMN TO TABLE; MOVED "VOLTAGE COLOR CODE" COLUMN TO END OF TABLE PER DCN #13355. JMN	DJP	1/25/07
4	ADDED NEMA#L24-20R TO CHART PER DCN# 9003 PAC	TLS	10/01/01
3	REMOVED CANADIAN CATALOG PER DCN #7772. AMZ	DB	8/24/00
2	REVISED NOTE; REVISED SCREW TO TRI-DRIVE PER DCN 7633 RCM	DB	6/21/00
1	RELEASED PER DCN 5220-13 B.C.	DJP	03/12-98
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
20A 3-WIRE
TWIST-LOCK
FLANGE RECEPTACLE

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS N/A	DR. BY B.C.	APP. BY DJP
DECIMALS N/A	TR. BY	SCALE 1:1
ANGLES N/A	CHK'D BY DJP	DATE 02/12/98