



M-7899 9

CAT NO. & RATING PRINTED ON BLADE HOLDER, COLOR CODE BY VOLTAGE



NEMA NO.	RATING	POLE/WIRE	CAT. NO.	CONFIGURATION	VOLTAGE COLOR CODE
L5-30P	125V	2P/3W GROUNDING	HBL2611 HBL2611F HBL26CM11 [B] HBL2611BK [C]		YELLOW
L6-30P	250V	2P/3W GROUNDING	HBL2621 HBL26CM21 [B] HBL2621BK [C] HBL2621EBK [C][D]		BLUE
L7-30P	277VAC	2P/3W GROUNDING	HBL2631		GRAY
L8-30P	480VAC	2P/3W GROUNDING	HBL2641		RED
L9-30P	600VAC	2P/3W GROUNDING	HBL2651		BLACK

CORD CLAMP RANGE
 CORD: 16/3 - 8/3
 TYPE S
 14/3 - 10/3
 TYPE SJ
 DIAMETER RANGE:
 Ø .360-.930
 [9.14-23.62]

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
COVER	NYLON	BLACK
CORD CLAMP	NYLON	NATURAL
BLADE HOLDER	NYLON	NATURAL
RETAINER	POLY CARBONATE	CLEAR
BLADE	.070 BRASS	
WIRE CLAMP	.080 CRS	NICKEL PLATE
#10 TERMINAL SCREWS	BRASS	[A]
#10 GROUND SCREWS	BRASS	GREEN
ASSEMBLY FASTENERS	STEEL	ZINC PLATE
DUST SHIELD	TPE	BLACK

NOTES:

- ALL SCREWS ARE COMBINATION PHILLIPS/SLOTTED/ROBERTSON HEAD.
- ALL DEVICES ARE UL LISTED, CSA CERTIFIED AND FED SPEC.
- COMPONENT FINISHES:
 - [A] WHITE FINISH ON NEUTRAL BLADE WHEN USED.
 - [B] CM DEVICES (CORROSION RESISTANT) SAME AS ABOVE EXCEPT: COVER AND CORD CLAMP - YELLOW
TERMINAL SCREWS & BLADES - NICKEL PLATED
WIRE CLAMPS - BRASS, NICKEL PLATE
ASSEM FASTENERS - STAINLESS STEEL
 - [C] BK DEVICES SAME AS ABOVE EXCEPT ALL BLACK.
 - [D] E DEVICES PROVIDED WITH CORD CLAMP INSERTS.

SYM	REVISIONS	APP	DATE
9	ADDED DUST SHIELD TO LIST OF PARTS PER DCN 15875 SPN	DJP FJB	4/22/09
8	ADDED "HBL2621EBK" & "D" TO NOTE 3 PER DCN 14136 RCM	JPP	8/1/07
7	REMOVED TOLS. & REVISED DIMS. TO .XX [.X] PER DCN 11902 RCM	JPP	1/6/06

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
 30A 3-WIRE
 TWIST-LOCK PLUG

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS N/A	DR. BY B.C.	APP. BY ZIMM
DECIMALS N/A	TR. BY	SCALE NONE
ANGLES N/A	CHK'D BY ZIMM	DATE 3/2/98

LEGEND: [IN. | mm]