



M-8540 8



TERMINAL BLOCK FOR #16-#12 AWG SOLID OR STRANDED WIRE ONLY
TORQUE TO 5 IN.LB.

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
COVER	PVC/ABS	GRAY
FACEPLATE	PVC/ABS	GRAY
PLUG	PVC/ABS	GRAY
TERMINAL BLOCK	30A 300V	
CIRCUIT BREAKER	5A	
DIN RAIL BASE	PVC/ABS	GRAY

NOTES: (UNLESS OTHERWISE SPECIFIED)
 1) DIMENSIONS ARE: INCHES [MILLIMETERS]
 2) .XX TOLERANCES TO BE ± .03
 3) SUPPLIED WITH DUPLEX AND STYLELINE WALL PLATES.
 4) FOR USE WITH 35MM DIN RAIL

REV	DESCRIPTION	APP	DATE
8	CAT. NO. GFBF20GYLA WAS GRF5350GY PER DCN 14626 SPN DJP	DJP	3/18/09
7	CAT. NO. DRUB15 THRU DRUB15HCB, BR15GRY WAS CRT5252GYMN1. CAT. NO'S. DRUB20, DRUB20AC AND DRUB20ACCB5, BR20GRY WAS CR5352GY. PER DCN 14621 SPN JPP	JPP	3/10/08
6	ADDED DRUBTVSS15AC TO TABLE PER DCN 13368. ABS	JPP	9/6/06
5	ADDED "FOR #16-#12 AWG SOLID OR STRANDED WIRE ONLY" TO "TERMINAL BLOCK", METRIC EQUIVALENTS TO DIMENSIONS, NOTES 1-4, AND "SEE TABLE". REMOVED "UR" FROM FINISH COLUMN. CHECKED "NON-REPAIRABLE" BOX PER DCN #12944. JMN	DJP	7/19/06

CATALOG NO.	CATALOG NO. ELECTRICAL RATING	WIRING DEVICE		CIRCUIT BREAKER	DIN RAIL MTG.	COMMENTS	CATALOG NO.	CATALOG NO. ELECTRICAL RATING	WIRING DEVICE		CIRCUIT BREAKER	DIN RAIL MTG.	COMMENTS
		CATALOG NO.	RATING						CATALOG NO.	RATING			
DRUB15	15A,125V	BR15GRY	120V 15A	NO	VERTICAL		KP1GY		NONE				FACEPLATE
DRUB15CB5	5A,125V	BR15GRY	120V 15A	YES	VERTICAL		KP8GY		NONE				FACEPLATE
DRUB15H	15A,125V	BR15GRY	120V 15A	NO	HORIZONTAL		KP26GY		NONE				FACEPLATE
DRUB15HCB5	5A,125V	BR15GRY	120V 15A	YES	HORIZONTAL		KP7GY		NONE				FACEPLATE
DRUB20	20A,125V	BR20GRY	120V 20A	NO	VERTICAL		KP720GY		NONE				FACEPLATE
DRUBGF115	15A,125VAC 60Hz CLASS A	D58718	120VAC 15A	NO	VERTICAL		DRUB20AC	20A,125V	BR20GRY	125V 20A	NO	VERTICAL	
DRUBGF115CB5	5A,125VAC 60Hz CLASS A	D58718	120VAC 15A	YES	VERTICAL		DRUB20ACCB5	5A,125V	BR20GRY	125V 20A	YES	VERTICAL	
DRUBGF115H	15A,125VAC 60Hz CLASS A	D58718	120VAC 15A	NO	HORIZONTAL		DRUBGF120	20A,125VAC 60Hz CLASS A	GFR5352GY	125VAC 20A	NO	VERTICAL	
DRUBGF115HCB5	5A,125VAC 60Hz CLASS A	D58718	120VAC 15A	YES	HORIZONTAL		DRUBGF120AC	20A,125VAC 60Hz CLASS A	GFR5352GY	125VAC 20A	NO	VERTICAL	
DRUBGF115AC	15A,125VAC 60Hz CLASS A	D58718	120VAC 15A	NO	VERTICAL		DRUBKITAC	20A MAX TOTAL 250V,600VAC MAX	NONE		NO	VERTICAL	
DRUBIG15	15A,125V	LCR5252IGGY	120V 15A	NO	VERTICAL		DRUBKITACCB5	5A MAX 250V,600VAC MAX	NONE		YES	VERTICAL	
DRUBTVSS15	15A,125VAC 60Hz	HBL5262GYSA	120VAC 15A	NO	VERTICAL		DRUBGF120BFAC	20A,125V 60Hz CLASS A	GFBF20GYLA	125VAC 20A	NO	VERTICAL	
DRUBKIT	20A MAX TOTAL 250V,600VAC MAX	NONE		NO	VERTICAL	3	DRUB1221AC	20A,120V-277V	CS1221GY	120V-277V 20A	NO	VERTICAL	
DRUBKITCB5	5A MAX 250V,600VAC MAX	NONE		YES	VERTICAL	3	DRUB5462	20A,250V	HBL5462GY	20A 250V	NO	VERTICAL	
DRUBTVSS15AC	15A, 125VAC, 60Hz	HBL5262GYSA	120VAC 15A	NO	VERTICAL	AUX CONTACT	DRUB5350GY	20A 125VAC 60Hz CLASS A	GRF5350GY	125VAC 20A	NO	VERTICAL	

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
CUSTOMER DRAWING
35MM DIN RAIL UTILITY BOX
HORIZONTAL & VERTICAL MTG.

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS ±1/64 DECIMALS ±.005 ANGLES ±2	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
	DR. BY PAC	APP. BY SM
	TR. BY	SCALE 1-1
	CHK'D BY SM	DATE 6-26-01

CODE 74545

DIMENSION SHEET FOR CAT. NO. SEE TABLE
 REPAIRABLE NON-REPAIRABLE
 M-8540
 8