



M-1323 3



NOTES: UNLESS OTHERWISE SPECIFIED

1. WIRE CAPACITY: #10-#6AWG SOLID OR STRANDED COPPER WIRE.
2. IP44 SUITABLE.
3. ALL DIMENSIONS TO BE INCHES [mm]

CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOLDER	PHENOLIC	
BODY	PET	
SLIDER	PHENOLIC	
CONTACT SPRING	COPPER ALLOY	
GROUND SHUNT	COPPER ALLOY	
PRESSURE TERM'S	COPPER ALLOY	
HINGE RIVET	ALUM ALLOY	
HOUSING	ALUM ALLOY	
FLAP	ALUM ALLOY	
GASKET	CLOSED CELL FOAM	

SUPERSEDES DWG
DATED 1/30/68

SYM	REVISIONS	APP	DATE
3	ADDED METRIC EQUIV TO ALL DIMS; ADDED NOTES 1 THRU 3; REMOVED ALL TOLS. FROM DIMS; ADDED 45° DIM; ADDED MATERIAL CALLOUTS FOR PARTS PER DCN #11902 RCM	JPP	1/6/05
2	1/20/98 REDRAWN ON CAD; REVISED PICTURE TO SHOW NEW FLAP; HINGE RIVET WAS EYELET; DECIMAL DIMS. WAS FRACTIONAL DIMS. PER DCN #5705 RCM	TCM	1/22/98

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
20A 250VDC, 30A 600VAC
4 WIRE HUBBELLOCK
ANGLE RECEPTACLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED
FRACTIONS $\pm$ 1/64
DECIMALS $\pm$.005
ANGLES $\pm$ 2°

WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
BRIDGEPORT, CT
DR. BY ASM APP. BY MDA
TR. BY RCM SCALE 1:1
CHK'D BY TCM DATE 1/20/98

DIMENSION SHEET FOR CAT. NO.
HBL21420

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-1323

3