



M-6071 5



NOTES: (UNLESS OTHERWISE SPECIFIED)

1) DIMENSION FORMAT IS: INCHES
(mm)CABLE DIA.
.375 MIN.
[11.68]
1.220 MAX.
[30.98]

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	SEE TABLE	
GASKET	RUBBER	
LOCK RING	POLYESTER	
INTERIOR	THERMOSET	
PINS	BRASS	
TERM. SCREWS	STAIN. STEEL	
BLAND CAP	POLYESTER	
BLANDS	RUBBER	
CLAMPS	POLYESTER	
CLAMP NUTS	BRASS	NICKEL
ASS'Y SCRS.	STAIN. STEEL	

5	ADDED CAT. NO. HBL430P6V02 AND SPECS. TO TABLE, PER DCN 18867 DOL	CAC	05/30/12
4	ADDED CAT. NO.'S HBL432P3W, HBL430P7V05, & HBL430P9V04, AND HOUSING/COLOR/MATERIAL COLUMN TO TABLE, ADDED Ø .38 HOLE TO VIEW WITH .80(20.3) & .44(11.2) DIM.'S, NOTE 1 WAS "1) DIMENSIONS ARE IN MILLI- METERS", CABLE DIA. .375 MIN. WAS .460 MIN., IN LIST OF PARTS "SEE TABLE" WAS "NYLON" PER DCN #6885. JMN	TCM	1/21/02
3	ADDED CAT. NO. FOR REVERSE SERVICE & "HBL" PREFIX PER DCN 6500 CAC		01/7/99 CAC
2	CHANGED FRACTIONAL DIMS TO DECIMAL DIMS. & REVISED LIST OF PARTS		7-18-91 A.J.L
1	CAT. NO. 432P6W WAS 430P6W & RATING REVISED		10-25-82 ASM
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICETITLE 30A & 32A 3 POLE
4 WIRE PIN & SLEEVE
PLUGSTOLERANCES UNLESS
OTHERWISE SPECIFIED.XX ± .01
.XXX ± .005
ANGLES ± 2°
DECIMALS ± .03WIRING DEVICE-KELLENS
HUBBELL INCORPORATED
SHELTON, CTDR. BY CAC APP. BY
TR. BY SCALE 1/2
CHK. BY DATE 1/6/99

CAT. NO.	CONFIGURATION	RATING	HOUSING		CAT. NO.	CONFIGURATION	RATING	HOUSING	
			COLOR	MATERIAL				COLOR	MATERIAL
					HBL430P7WR HBL430P7W		30A 3 Ø 480VAC	RED	NYLON
					HBL430P7V05		30A 3 Ø 480VAC	RED	VALOX
HBL432P3W		32A 380V-50HZ 440V-60HZ	RED	NYLON	HBL430P9WR HBL430P9W		30A 3 Ø 250VAC	BLUE	NYLON
HBL430P6V02		30A 380-415VAC	RED	VALOX	HBL430P9V04		30A 3 Ø 250VAC	BLUE	VALOX
HBL430P5W HBL430P5WR		30A 3 Ø 600VAC	BLACK	NYLON					
HBL432P6W		32AMP 380V-415VAC	RED	NYLON	HBL430P12W		30AMP 125/250VAC	ORANGE	NYLON

CODE 74545

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-6071

U