





M-6074 5

NOTES: (UNLESS OTHERWISE SPECIFIED)

1) DIMENSION FORMAT IS: INCHES
[mm]

2) DIMENSIONS SHOWN ON THIS DRAWING ARE
NOMINAL VALUES FOR GENERAL USE ONLY.
ACTUAL PART TOLERANCES MUST BE
OBTAINED FROM HUBBELL ENGINEERING.

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
1. HOUSING	SEE TABLE	
2. GASKET	RUBBER	
3. LOCK RING	POLYESTER	
4. INTERIOR	THERMOSET	
5. PINS	BRASS	
6. TERM. SCRS.	STAIN. STEEL	
7. FLANGE	NYLON	
8. ASS'Y SCRS.	STAIN. STEEL	

CAT. NO.	CONFIGURATION	RATING	HOUSING		CAT. NO.	CONFIGURATION	RATING	HOUSING	
			COLOR	MAT'L				COLOR	MAT'L
					HBL430B7W		30A 3Ø 480 VAC	RED	NYLON
					HBL430B9W		30A 3Ø 250 VAC	BLUE	NYLON
HBL430B5W		30A 3Ø 600 VAC	BLACK	NYLON					
HBL432B6W		32 AMP 380-415 VAC	RED	NYLON	HBL430B12W		30 AMP 125/250 VAC	ORANGE	NYLON
HBL430B6V02		30A 380 - 415 VAC	RED	VALOX					

TITLE

30 & 32 A. 3 POLE 4 WIRE
PIN & SLEEVE INLETS

TOLERANCES UNLESS
OTHERWISE SPECIFIED

DECIMALS ± .03
ANGLES ± 2°

HARVEY HUBBELL, INC.
BRIDGEPORT, CONN.

DR. BY W.T.C. APP. BY
TR. BY SCALE: 1"=1" CHCD. BY DATE 5/5/80

CODE 74545

DIMENSION SHEET FOR CAT. NO. SEE TABLE
 REPAIRABLE ☐ NON-REPAIRABLE ☒ **B**
M-6074
5