

Part No.	Cable color
~088*1~	GRAY
~088*2~	BLACK
~088*3~	WHITE

NOTE ① We indicate the length of the harness on the last of product name. 'L' part.


② Tolerance for [ L ]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	$\pm 4$
$200 < L \leq 500$	$\pm 8$
$500 < L \leq 1000$	$\pm 12$
$1000 < L$	$\pm 1.5\%$

③ Connector rotation angle is within  $\pm 45$  degree from the above image. For long length in the case of  $L > 500$ , the angle is optional.

4. Specifications are subject to change without notice.

【 DIMENSIONS OF CONNECTOR 】



1	U.FL-LP-088	CL331-0454-0	2	1.37 Dia. coaxial cable
NO.	PART NO.	CODE NO.	NO.	PART NO.

UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
<b>HRS</b> HIROSE ELECTRIC CO., LTD.			APPROVED :NK. NINOMIYA 16.07.22 CHECKED :MT. KANEKO 16.07.21 DESIGNED :MS. MATSUMOTO 16.07.21 DRAWN :MS. MATSUMOTO 16.07.21	DRAWING NO. U.FL-2LP-088**T-A-L		
						① ①/1