


ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	TPU	BLACK
2	HOUSING	BRASS	NICKEL PLATED
3	CONTACT	BRASS / GOLD	CuZn Ni/ Au
4	LOCK NUT	STEEL	ZINK PLATED
5	O-RING	VITON	RED
6	O-RING	NBR	BLACK
7	WIRES	COPPER/PVC	SEE TABLE

- 1 - BROWN
- 2 - WHITE
- 3 - BLUE
- 4 - BLACK
- 5 - GREY

POLE	MATERIAL NO	ENGINEERING NO	FINISHED LENGTH
4	1200840007	WR4000A18C300	300 mm
5	1200840016	WR5000A18C300	300 mm



VOLTAGE RATING: 250 VAC/VDC
 AMPERAGE RATING: 4A
 PROTECTION CLASS: IP 67/68/69K
 OPERATING TEMPERATURE: -25°C / 90°C
 UL CERTIFICATION: FILE NO. E152210
 CSA CERTIFICATIONS: FILE NO. LR6837

ENTER DESCRIPTION EC NO: WEU2010-0369 DRWN:STAUDIGEL 2010/02/17 CHKD: 2010/02/19 APPR:FPACHER 2010/02/24	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
	▽=0	mm INCH	IN/MM	2:1	INCH	
	∇=0	4 PLACES ± --- ± ---	DRAWN BY DATE	TITLE		
		3 PLACES ± --- ± ---	NSTAUDIGEL 2010/02/17	M12 4/5P UL FEM REC FRONT MOUNT 1/2NPT		
	2 PLACES ± 0.05 ± ---	CHECKED BY DATE	APPROVED BY DATE			
	1 PLACE ± 0.1 ± ---		FPACHER 2010/02/19			
	ANGULAR ± ---°	MATERIAL NO.	DOCUMENT NO.			
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
		A3		SD-120084-027		SHEET NO. 1 OF 1