

TECHNICAL CHARACTERISTICS

MATERIAL

INSULATOR: LCP
FLAMABILITY RATING: UL94-V0
COLOR: BLACK
CONTACT MATERIAL: COPPER ALLOY
CONTACT TYPE: STAMPED
CONTACT PLATING: TIN
QUALITY CLASS: 25 MATING CYCLES
PITCH: 3.00MM

ENVIRONMENTAL

OPERATING TEMPERATURE: -40 UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL

CURRENT RATING: 5A
WORKING VOLTAGE: 250V AC
INSULATOR RESISTANCE: >1000 MOHM
DIELECTRIC WITHSTANDING VOLTAGE: 1500V AC/MN
CONTACT RESISTANCE: 10 mOHM MAX

STANDARD

 CERTIFIED: E323964

SOLDERING



JEDEC LEAD FREE REFLOW SOLDERING PROCESS



PACKAGING


TUBE

DIMENSION

A = 3.00 x (NB. PIN / 2 - 1)
B = 3.00 x (NB. PIN / 2 + 1) + 0.70

RoHS Compliant				<div>PROJECTION: </div>	<div>GENERAL TOLERANCE .X = \pm 0.2 .XX = \pm 0.15</div>	<div> WÜRTH ELEKTRONIK</div>	
				APPROVAL: BBu	UNIT: MM	DESCRIPTION: 3.00MM MALE DUAL ROW SMT RIGHT ANGLE HEADER WITH THROUGH HOLE RETENTION METAL CLIP	SIZE A4
I	02-JUL-15	PINNING	AK		SCALE:		
H	19-JAN-15	PROJECTION	QP		SHEET: 1/3		
REV	DATE	FILE	BY		DRAW: JACK		
						WERI PART NO: 662 0xx 230 822	







Note:

1,Dimension
 Tube Size: L=635mm
 Inner Carton Size:650(L)X140(W)X125(H) (mm)
 Carton Size:660(L)X270(W)X300(H) (mm)



2,Quantity:
 42 Tube/Inner Carton
 4 Inner Carton/Carton

Pin.	Pcs/Tube	Pcs/Inner carton	Pcs/Carton
2	91	3822	15288
4	63	2646	10584
6	48	2016	8064
8	39	1638	6552
10	32	1344	5376
12	28	1176	4704
14	24	1008	4032
16	22	924	3696
18	20	840	3360
20	18	756	3024
22	16	672	2688
24	15	630	2520

INNER CARTON

CARTON

RoHS Compliant							
G				PROJECTION: 	GENERAL TOLERANCE .X = ± 0.2 .XX = ± 0.15		
F							
E							
D							
C				APPROVAL: BBu	UNIT: MM	DESCRIPTION: 3.00MM MALE DUAL ROW SMT RIGHT ANGLE HEADER WITH THROUGH HOLE RETENTION METAL CLIP WERI PART NO: 662 0xx 230 822_TPK	SIZE A4
B					SCALE:		
A					SHEET: 2/3		
REV	DATE	FILE	BY		DRAW: PEARL		

