

D-SUB TECHNICAL DATA

D

Flame retardant to UL94 V-0 Color Black

CONTACTS : brass.

Gold flash over 1.25um (50u") min nickel

ELECTRICAL : Voltage rating :1000 V RMS at 50 Hz

Current rating 5A.

Insulation resistance >1000 M Ohms

Contact resistance 20 mOhms max.

CLIMATIC : Temperature range -55°C up to 125°C

MARKING : Amphenol-...(Series No.)

Commercial reference

Manufacturing date

9

W

PRODUCT CODE

L 77 SD D 50 S

RoHS Compliance

77: tinned shell for
receptable

SD: standard density
HD: high density

Shell Size :D

Contact type:
S:Female
P: Male

Configuration: 50

A

