


This document is the property of Amphenol Connector and is intended for use only for the specific application and product identified. It is not to be distributed, reproduced or used in any other manner without the prior consent of Amphenol Connector. All rights are reserved in this document.




REVISIONS		DATE	APPROVED
S/N	ECN		
B		12/01/07	

**D-SUB TECHNICAL DATA**

**Product Specification**  
 Material :Glass-Filled Thermoplastic PBT,UL94V-0 rated  
 Insulator :Copper alloy  
 Contact :SPCC  
 Shell :SPCC  
**Electrical**  
 Contact Resistance :20 milliohms  
 Max at 1 AMP DC.  
 Insulation Resistance :1000  
 megohms at 500 VDC  
 Dielectric Withstanding Voltage :  
 1000 VAC/rms 60Hz for 1 minute  
 Current Rating :1 AMP  
 Voltage Rating :250 VAC/rms 60Hz

**PRODUCT CODE**



UNLESS OTHERWISE SPECIFIED		APPROVAL DATE		TITLE
TOLERANCES	METRIC	DATE	BY	
U.S.	0.50	12/01/07		Amphenol
METRIC	0.20			
DRAWN BY: [Signature]				
CHECKED BY: [Signature]				
DATE: 12/01/07				
DRAWING FILE: [Blank]				
FOR MATERIALS AND FINISHES: [Blank]				
SEE NOTES REGARDING DIMENSIONS: [Blank]				
DIMENSIONS: [Blank]				
TOLERANCES: [Blank]				
FINISH: [Blank]				
ANGLE OF PROJECTION: [Blank]				
SIZE: A4				
SCALE: NONE				
SHEET 1 OF 1				
S-SUB connector, HD series				