



DIT IS ONZE EIGENDOM EN MAG NOCH NAGEMAAKT, HERDRUKT, OVERGEMAAKT AAN DERDEN, NOCH VOOR FABRIKATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE TOELATING. BIJ NIET GEBRUIK IS DE TERUGZENING VERPLICHT.

THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY, NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO JS IN CASE OF NO USAGE

BS,A , 202363,007,00

REV.	DATE	DESCRIPTION	BY	C'K'D'
00	18.08.97	REDRAWN FROM DRAWING BSA 062110 SHEET 7	S.V.D.	



MATERIAL :

BODY : POLYESTER 30% GLASSFILLED , UL94V-0,
COLOUR : BLACK
CONTACTS : BRASS, GOLD OR TIN PLATED

PERFORMANCE CHARACTERISTICS :

OPERATING TEMPERATURE : -55°C TO 105°C
INSULATING RESISTANCE : 5000 MΩ MIN.
TEST POTENTIAL : 2000 VAC

NOTES :

- CONNECTOR SUPPLIED FULLY LOADED WITH MACHINED PIN CONTACTS.
AU PLATED : SMS36GE4, AU FLASH :
SMS36GE4J, TIN PLATED : SMS36GE4T
- MATING PART SMS36P1 PLUG
- PC-BOARD THICKNESS : 2.4 MM
- DRILLING HOLE PATTERN : SEE BS,A ,200597,008

GEN. ST.	01	02	03	04	05	06	07	08	0D	50	60	70	80	90																	
INT. ST.	10	11	12	13	14	18	20	31	32	33	34	38	39	40	42	43	44	45	46	48	56	70	72	73	75	76	81	82	83	84	88

1DEC ±0,2 1DEC 2DEC ±0,1 2DEC ANGLES ±1° HOEKEN	APPR. DRAFT CHECKED PROD. MGR. PR. ENG. MGR. PR. MGT. MGR.	DATE 18-08-97	SIGN. S. Van Dessel	SMS QIKMATE STRAIGHT MALE REC. WITH MACH. CONT. CAT. No. SMS36GE4* SOURIAU Connection Technology SOURIAU Route Nationale 23 72470 CHAMPAGNE SCALE 2 / 1		
WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE. ALL DIMENSIONS IN MM	REFERENCES / REFERENTIES			BS , A , 202363 , 007 , 00 DRAWING NR. CUSTOMER DRAWING		
ALLE AFMETINGEN IN MM						