



DIT IS ONZE EIGENDOM EN MAG NOCH NAGEMAAKT, HERDRUKT, OVERGEMAAKT AAN DERDEN, NOCH VOOR FABRIKATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE TOELATING. BIJ NIET GEBRUIK IS DE TERUGZENDING VERPLICHT.

THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY, NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO JS IN CASE OF NO USAGE

BS,A , 202362,004,01

REV.	DATE	DESCRIPTION	BY	C 'K 'D '
00	18.08.97	REDRAWN FROM DARWING BSA 062109 SHEET 4	S.V.D.	
01	12.09.97	BEC 9.3390	S.V.D.	



DRILLING HOLE PATTERN

MATERIAL :

BODY : POLYESTER 30% GLASS FILLED, UL94V-0, COLOUR : BLACK

CONTACTS : CONTACT BODY : BRASS, GOLD OR TIN PLATED

INNER SPRING : BERYLLIUM COPPER, GOLD OR NICKEL PLATED

PERFORMANCE CHARACTERISTICS :

OPERATING TEMPERATURE : -55°C TO 105°C

INSULATING RESISTANCE : 5000 MΩ MIN.

TEST POTENTIAL : 2000 VAC

NOTES :

1.CONNECTOR SUPPLIED FULLY LOADED WITH MACHINED SOCKET CONTACTS.

GOLD PLATED : SMS6GE3 ; GOLD FLASH : SMS6GE3J ; TIN PLATED : SMS6GE3T


2.MATING PART SMS6P1 PLUG

3.PC-BOARD THICKNESS : 2.4 MM

4.DISCRIMINATION IS GUARANTEED WITHOUT LOSS OF CONTACT POSITION WHEN USING SMSPK63

DISCRIMINATION PINS. FOR TECHNICAL INFORMATION ABOUT SMSPK63 : SEE BS,C ,201424,003.

GEN. ST.	01		02		03		04		05		06		07		08		0D		50		60		70		80		90				
INT. ST.	10	11	12	13	14	18	20	31	32	33	34	38	39	40	42	43	44	45	46	48	56	70	72	73	75	76	81	82	83	84	88

1DEC ±0,2 1DEC 2DEC ±0,1 2DEC ANGLES ±1° HOEKEN	APPR.	DATE	SIGN.	SMS QIKMATE STRAIGHT FEMALE REC. WITH MACH. CONT.	
WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE.	DRAFT	18-08-97	S.Van Dessel	CAT. No. SMS6GE3*	
	CHECKED			 SOURIAU Connection Technology	SOURIAU Route Nationale 23 72470 CHAMPAGNE
	PROD. MGR.				
ALL DIMENSIONS IN MM	PR. ENG. MGR.			2 / 1	
	PR. MGT. MGR.			BS, A , 202362, 004, 01	
	REFERENCES / REFERENTIES			DRAWING NR. CUSTOMER DRAWING	
ALLE AFMETINGEN IN MM					