

BRAZED SEAM

STAMP AMP 16-14* APPROX AS SHOWN

COPPER PER ASTM B-152, ANNEALED

TIN PLATE 0.00254 [.000100] MIN THK PER
ASTM B-545

MEETS M7928/7-8, CLASS 1 & 2

MEETS M7928/7-8, CLASS 2

6 REC