


HONEYWELL
PART NUMBER

WA-2RQ1-D6

REV	DOCUMENT	CHANGED BY	CHECK
B	0048645	KNR 06FEB09	CMH



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000±.002 CENTERS
- 2 HARDWARE FURNISHED UNASSEMBLED

CATALOG LISTING
WA-2RQ1-D6
ABM5000REPLACES:
X201720 - WA

CHARACTERISTICS	ELECTRICAL DATA
OPERATING FORCE— — — — 14—22 OZ	CONTACT ARRANGEMENT S P N C
RELEASE FORCE— — — — 10 OZ MIN	L23 20A - 125, 250 OR 480 VAC 10A - 125 VAC "L" 1HP - 125 VAC, 2HP - 250 VAC 1/2A - 125 VDC, 1/4A - 250 VDC
DIFFERENTIAL TRAVEL— — — .002—.0075	L288 L308 L315
OVERTRAVEL— — — — —.219 MIN	20(3)A 250V ~ T85 5E4

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:

NO PLACES	X	±	-
ONE PLACE	.X	±	.030
TWO PLACE	.XX	±	.015
THREE PLACE	.XXX	±	.005
ANGLES	X	±	-

THIRD ANGLE PROJECTION



DRAWN	SSK	30JAN09
CHECK	CMH	30JAN09

THIS DRAWING COVERS A PROPRIETARY ITEM
AND IS THE PROPERTY OF HONEYWELL.
THIS DRAWING IS NOT TO BE COPIED OR USED
WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ASME Y14.5M-1994
OTHER HONEYWELL ENGINEERING
STANDARDS MAY APPLY

RASTER

Honeywell

TITLE

SWITCH - BASIC

SIZE	TYPE	CAGE CODE	DRAWING NAME	REV
B	I	-	WA-2RQ1-D6	B
SCALE	NONE		SHEET	I OF I