




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF AMPHENOL LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY AMPHENOL LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE313C0041	2013-11-26	Tom_gu	Change Tolerance And Length

ALTW
CONFIDENTIAL
 2013-11-26
R&D DEPT.





Waterproof Rate: IP67

UA-30PMF-LD7B XX

△ XX	150~300mm
15	:150mm
20	:200mm
30	:300mm

- * Ⓞ Important Dimension. Cable Length(L):150~300mm
- * Housing: ABS, Black
- * Screw Nut: Nylon+GF, Black
- * Gasket: Silicone, Gray
- * Jack: USB3.0-A Female Solder
- * Cable: USB 3.0, (1P*28#+D+Al/My)*2+1P*28#+2C*28#+F+Al+B, PVC Jacket, UV Resistant, OD=5.5mm, Black
- * Cable Length Tolerance: 150MM~300MM:±15mm
- * Use with waterproof cap or dust cap Panel Thickness max: 2.8mm
- * Use without waterproof cap or dust cap Panel Thickness max: 4.0mm
- * All of Drain twisted together.

ALTW
 DCC. DEPT.
 CONFIDENTIAL
 2013.12.06
ISSUED



Shield	Braid	編織	Shield	
9	Orange 28AWG	橙	9	Twist
8	Purple 28AWG	紫	8	
7	Drain 28AWG	地線	7	Twist
6	Yellow 28AWG	黃	6	
5	Blue 28AWG	藍	5	Twist
	Drain 28AWG	地線		
4	Black 28AWG	黑	4	Twist
3	Green 28AWG	綠	3	
2	White 28AWG	白	2	Twist
1	Red 28AWG	紅	1	
Conn.1	Wire Color		Conn.2	
	Pin Out			

UNIT: mm

TOLERANCE	
.X	±0.25
.XX	±0.1
.XXX	±0.05
ANGLES	±1°

TITLE: USB3.0 Female Lock To A Plug

SCALE	1:1	SIZE	A4	SHEET	1	OF	1
REV.	B	RC-REV.	A.1	Ⓞ	Inspection item		

Amphenol LTW
 安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Tom_gu	2013-11-26
DWG NO	CHECKED BY	DATE
UA-30PMF-LD7BXX	Mafei	2013-11-26
CUSTOMER	APPROVED BY	DATE
ALTW	Victor	2013-11-26