Part number	Wire range AWG	Color	Maximum insulation diameter	PRESSES & APPLICATORS: CP-861, CP-860, CP-851, CP-862
DNF18-250FIM-2K	22-18 (0,5-1,0)	Red	.133 (3.38)	CD-800-4, CA9-4B
DNF14-250FIM-2K	16-14 (1,5-2,5)	Blue	.158 (4.01)	CD800-5, CA9-5B

Notes:

- 1. Used for:
 - A. 600 V maximum rating
 - B. 221°F (105°C) maximum temperature rating (CSA)
 - C. 257°F (125°C) maximum temperature rating (UL)
 - D. Stranded copper wire only
- 2. Wire strip length: $9/32^{+1/32}_{-0}$ (7.1 +.8 _-0)
- 3. Material:
 - A. Stamping .016 thick nickel plated brass
 - B. Housing Nylon
- 4. Package quantity:
 - -2K = 2000 pieces on continuously molded carrier strip
- 5. Dimensions in brackets are in millimeters or mm²

DESCRIPTION






CUST

РМ

DSM



.420 (10.66)

A41104_08

NONE

A41104

LM

						7141104_00			
08	8 12/03 KLFU			UPDATED WIRE RANGE ON DNF18 FROM 1.5 TO 1,0 CLARIFIED TOOLING CHART	11363			1 VALUALILIZA	
07	1/01	SAB	I	FILESPEC WAS N41104AA_PCD_06	-		-	ZAMUUUU corp.	TINLEY PARK, ILLINOIS

06 7/99 ED SKB ADDED CP-862 & CA9 07848 TR0 JCJ Disco™ Termo™ fully insulated male disconnects
05 1/99 JD JW Material was tin plated. 07402 LD LCA .250 X .032 Tab size

ECN

REV DATE

BY

CHK