

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00	C	REVISED PER ECO-13-017159	23DEC2013	KH SB

1 PLUG ACCEPTS 22 DF PIN CONTACTS. CONTACTS MUST BE PURCHASED SEPARATELY.
 2 ALL PARTS SHIPPED UNASSEMBLED, EACH PART INDIVIDUALLY BULK PACKED.
 3 FLAME RETARDANT 94V-0 RATED, STYRENE POLYOLEFIN OR PVC, BLACK.
 4 FLAME RETARDANT 94V-0 RATED, GLASS FILLED NYLON OR POLYESTER, BLACK.
 5 CARBON STEEL.
 6 .000200 MIN. TIN PLATE OVER .000100 MIN COPPER UNDERPLATE.
 7 ZINC NICKEL, TRIVALENT BLACK.
 8 CARBON STEEL, C1022.

EXPANDING NECK, ACCOMMODATES CABLE FROM .190-.375 DIA

1.685 MAX

FERRULE, MUST BE PURCHASED SEPARATELY, AS REQUIRED BY CABLE DIAMETER

4-40 JACKSCREW QTY: 2

SHIELD QTY: 2

ENCLOSURE

PLUG CONNECTOR HDP-22

1.467 TYP

.812 TYP

.630 MAX

CABLE REF

.125 MAX

1.640 MAX

1.312

2	W/ LOGOS	1658679-1
PACKAGING	REMARKS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. BAUM 02JAN04		
DIMENSIONS: INCHES		CHK S. BOLASH 02JAN04		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. WALMSLEY 02JAN04	NAME	
0 PLC ± -		PRODUCT SPEC 108-1268	SHIELDING ENCLOSURE KIT, PLUG, SIZE 2, 26 POSN, HDP-22, AMPLIMITE™	
1 PLC ± -		APPLICATION SPEC 114-10001	SIZE A2	CAGE CODE 00779
2 PLC ± -		WEIGHT -	DRAWING NO C-1658679	RESTRICTED TO -
3 PLC ± .005		CUSTOMER DRAWING		
4 PLC ± -		SCALE 2:1	SHEET 1 of 1	REV C
ANGLES ± 2°				
FINISH				

1471-9 (3/11)