

REV	DOCUMENT	CHANGED BY	CHECK
11	207690	SAV 19MAR03	MDM

GL

BODY STYLE CODE	
CODE	DESCRIPTION
C	METAL MinDIN - EN550047
D	PLASTIC MinDIN - EN550047
E	PANCAKE MinDIN - EN550047

CONDUIT STYLE CODE

BASIC SWITCH CODE

OPERATING HEAD CODE	
CODE	DESCRIPTION
A1	SIDE ROTARY - FIXED LENGTH LEVER
A2	SIDE ROTARY - ADJ. LENGTH LEVER
A4	SIDE ROTARY - ADJ. LENGTH ROD
A5	SIDE ROTARY - OFFSET LEVER
A9	SIDE ROTARY - CERAMIC ROLLER
B	TOP PIN PLUNGER
C	TOP ROLLER PLUNGER
D	TOP ROLLER ARM
E7B	WOBBLE
K8	WHISKER

OPERATOR (LEVER) CODE


INSTALLATION DRAWING (NEWHOUSE SCOTLAND DRAWING)			
OPER HEAD CODE	BODY STYLE CODE		
	C	D	E
A1	MTG-GL-167	MTG-GL-172	MTG-GL-177
A2	MTG-GL-191	MTG-GL-192	MTG-GL-193
A4	MTG-GL-194	MTG-GL-195	MTG-GL-196
A5	MTG-GL-197	MTG-GL-198	MTG-GL-199
A9	MTG-GL-211	MTG-GL-212	MTG-GL-213
B	MTG-GL-168	MTG-GL-173	MTG-GL-178
C	MTG-GL-169	MTG-GL-174	MTG-GL-179
D	MTG-GL-170	MTG-GL-175	MTG-GL-180
E7B	MTG-GL-171	MTG-GL-176	MTG-GL-181
K8	MTG-GL-205	MTG-GL-210	MTG-GL-209

"FOR APPROPRIATE INSTALLATION DRAWING, CONSULT NEWHOUSE SCOTLAND DRAWING LISTED IN CHART"

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:

	<input type="checkbox"/> US (inch) CUSTOMARY	<input checked="" type="checkbox"/> SI (mm) METRIC
NO PLACE	X	±.040 ±1
ONE PLACE	.X	±.030 ±0,4
TWO PLACE	.XX	±.015 ±0,15
THREE PLACE	.XXX	±.005 ±
ANGLES		±
RAW MATERIAL-COMMERCIAL STANDARD		

THIRD ANGLE PROJECTION



DRAWN	GLH	19MAR03
CHECK	MDM	19MAR03
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED		
PTC 2D	ASME Y14.5M-1994	

Honeywell			
TITLE SWITCH, LIMIT			
SIZE	DWG TYPE	DRAWING NAME	REV
B	I	GL SERIES CHART 3	11
SCALE	NONE	WEIGHT	SHEET 1 OF 1