



		P1	Pin Assignment	P2
	(A4,B4,A9,B9) VBUS		RED	1
	(A7) D-		WHITE	2
	(A6) D+		GREEN	3
	(A1.B1.A12.B12) GND		BLACK	4
	(A5) CC			NC
	(A3) SSTxn1		ORANGE	5
	(A2) SSTxp1		Purple	6
			Drain	7
	(B10) SSRxn1		BLUE	8
	(B11) SSRxp1		YELLOW	9
	Shell		SHIELD	Shell

⑫	A0040411-00002	Low pressure molding compound, transparent color, hardness, 40 ~ 48 d	1	g
⑪	A0020100-00174	USB TYPE C-On the tin plating nickel to clamp (one)	1	PCS
⑩	A0020100-00175	USB TYPE C-The tin plating nickel to clamp (one)	1	PCS
⑨	A10-R042106	W=5MM 25u Double conductive copper foil	0.02	M
⑧	A10-R075004	Heat shrinkable casing-φ2.0mm-black	0.035	M
⑦	A5-R047011	transparent PE ROHS LDPE	3	g
⑥	A5-R047001	45P BLACK PVC ROHS	12	g
⑤		TYPE C-USB 3.0 C Type Connector With-Empty PCB + patch (56 k resistor)	1	PCS
④	A6-R106104	USB 3.0 A (M) after automatic welding nickel plated iron shell (for wire diameter 5.0 5.5 mm)	1	PCS
③	A6-R106110	USB 3.0 A (M) before the automatic welding iron shell plating nickel	1	PCS
②	A2-R029103	USB 3.0 A(M) 9P The three type blue rubber core welding line	1	PCS
①	A0010307-00097	USB3.0~UL2725~[30AWG (7/0.10TC)+EAM]*2P+[30AWG (7/0.10TC)+A]*1P+24AWG (7/0.20TC)*2C+AEB (16/7/0.12TC 85%)OD:4.5MM~Black PVC~No Marking	1	M
NO	ITEM	DESCRIPTION	Q'TY	UNIT

REV	ECN	DESCRIPTION				DATE	NAME
	TOLERANCE						
	INCHES	M/M					
	.X	.015 .30					
	.XX	.010 .10					
.XXX	.005 .05	TITLE: USB 3.1 AM TO CM CABLE(10G) L=1.0M					
DRAWN BY	zhouwenlong		CUSTOMER :		CPC		
			CUSTOMER P/N:		PSG91480		
CHECK BY			SCALE	NONE	DRAWING NO:		REV A01
			UNIT	MM			
APPD BY			DATE	2017.05.02			