






REV	DESCRIPTION	DRAWN	DATE
A	Δ 6.10 $\pm$ 6.00 $\pm$ 0.03	Rus	12/06/01
B	All TFE & Bu Contact	BB	12/18/06



Panel cutout

10	Washer(W-002)	1	Brass	Nickel
9	Nut(N-001)	1	Brass	Nickel
8	Press it washer(W-001)	1	Brass	Nickel
7	Dielectric(D-001)	1	Teflon	White
6	Dielectric(T-02016)	1	Teflon	White
5	Dielectric(T-02015) Δ	2	Teflon	White
4	Pin(C-02020)	1	Beryllium	Gold
3	Body(B-02003)	1	Brass	Black Chrome
2	Body(B-02002)	1	Brass	Nickel
1	Body(B-02001)	1	Brass	Nickel
NO	Description	Q'ty	Material	Finish

UNLESS OTHERWISE SPECIFIED
 1.REMOVE ALL BURRS.
 2.BREAK ALL CONNERS & EDGES CO.15 MAX.
 3.CHAMFER 1ST & LAST THREADS 45°.
 4.DIAMETERS ON COMMON CENTERS.
 5.ALL DIMENSIONS ARE TO BE CONCENTRIC WITHIN 0.1 T.I.R.
 6.ALL DIMENSIONS ARE AFTER PLATING.

* MAJOR DIMENSION
 UNLESS OTHERWISE NOTED TOLERANCES
 0.5-6= $\pm$ 0.2
 6-30= $\pm$ 0.4
 30-120= $\pm$ 0.6
 120-315= $\pm$ 1.0
 ANGLES= $\pm$ 1°

SCALE 3/1 UNIT MM

APPROVED
 CHECKED
 DRAWN Russell
 DRAWN DATE 08/27/01

Bomar Interconnect Products, Inc.
 TITLE DOUBLE BNC FEMALE BULKHEAD 75ohm
 DRAWING NO. HBC335R744
 REV A
 FILE NO. D:\DWG\COMPOSE\BNC\BNC-1354-4-75ohm