


PCB layout, component side



Max. Temperature: 260°C during 10 seconds.
Find further technical information on DS 09550200302.

0955 215 6612 333	2	4-40 UNC	Black insulator	Samples
0955 215 3612 741	1			Reel packaging (140 connectors)
0955 215 6612 741	2			
0955 215 7612 741	3			
0955 215 3611 741	1	M3		
0955 215 6611 741	2			
0955 215 7611 741	3			
Part number	PL	Nut		Index designation

	All rights reserved Department EC PD - CN HARTING Electronics GmbH D-32339 Espelkamp	All Dimensions in mm Original Size DIN A3	Scale 2:1 Free size tol.	Ref. Sub.
		Created by ZENG Inspected by LUOK Standardisation HOFFMANN Date 2016-08-29 State Final Release	Title D-Sub straight SMT 15-pole female ass with screw nut and pad	Doc-Key / ECM-Nr. 100236643/UGD/001/B 500000107668
Type TB	Number 0955215X61X	Rev. B	Page 1/1	