


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G1	REVISED PER ECR-16-010133	14JUL2016	NK	DC



- 1 CONTINUOUS STRIP ON REELS.
- 3 WIRE SIZE 0.3–1.3mm² [22–16] AWG.
- 4 INSULATION RANGE $\phi 2.54$ –3.56 [$\phi .100$ –.140].

							61588-1	
							PART NO	
F OR O OR OV	4.57 [.180] (F AND O)	6.35 [.250]	F	2.54 [.100]	2.11 [.083]	1.3mm ² [16]	THIS DRAWING IS A CONTROLLED DOCUMENT. DWNjr ruth19JAN08 CHKD DECKER19JAN09 APVDD DECKER19JAN09 PRODUCT SPEC APPLICATION SPEC WEIGHT— CUSTOMER DRAWING TE Connectivity RING SIZEA3CAGE CODE00779DRAWING NOG-61588RESTRICTED TO— SCALE5:1SHEET1 OF 1REV G1	
	3.94 [.155] (OV)				1.96 [.077]	0.8mm ² [18]		
					1.85 [.073]	0.5mm ² [20]		
					1.80 [.071]	0.3mm ² [22]		
TYPE	WIDTH	STRIP LENGTH ± 0.38 [.015]	TYPE	WIDTH	HEIGHT ± 0.05 [.002]	WIRE	MATERIAL#4 HARD BRASSFINISHTIN	
INSUL BARREL CRIMP			WIRE BARREL CRIMP					