




LOC		DIST		REVISIONS					
—		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
					T	REV PER ECO 15-016064	11-9-15	CT	CD



1. THIS RECEPTACLE WILL MATE WITH ANY PLUG CONNECTOR WITH THE SAME INSERT ARRANGEMENT AS DEFINED BY MS18276-1.
2. MAXIMUM WIRE INSULATION USED WITH THIS RCPT. IS .072 DIA. MAX.
3. Be-Cu RETENTION CLIPS ARE INCLUDED IN INSERTS.
4. FAR SIDE REFERS TO WIDE SIDE OF KEYSTONE.
5. UL/CSA DESIGNATION STAMPED IN THIS AREA,OPTIONAL
6. RESTRICTED TO CAE ELECTRONICS ONLY.
7. THESE CONNECTORS ARE QUALIFIED TO GODDARD SPACE FLIGHT CENTER SPECIFICATION S-311-P-4.
8. CONNECTOR SUPPLIED WITH CONTACTS, AMP PART NUMBER 206793-1; (NOT INSTALLED).



OBSOLETE	4	.120	570513-4	206803-9
	5	.120	LMSC 1621480-004	206803-8
	6	.120	LMSC 1621480-004	206803-7
	7	.120	311P409-4S-B-12	206803-6
	8	.120	2A014-009V-001	206803-4
		.154		206803-3
		.120	311P409-4S-B-12	206803-2
		.154	311P409-4S-B-15	206803-1
REMARKS		DIA A	INK STAMPED CUSTOMER P/N	INK STAMPED AMP P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MANJUNATH G M 27-May-15	TE Connectivity	
DIMENSIONS: INCHES		CHK CHARLES THOMAS 27-May-15	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD CHARLES THOMAS 27-May-15	RECEPTACLE FOR SOCKET CONTACT,	
		PRODUCT SPEC	SIZE 4, 37 POS. (NON-MAGNETIC)	
0 PLC ± .		APPLICATION SPEC	SIZE	CAGE CODE
1 PLC ± .		—	DRAWING NO	
2 PLC ± .		—	RESTRICTED TO	
3 PLC ± .005		—	A1 00779 C=206803	
4 PLC ± .		—	—	
ANGLES ± .		—	—	
FINISH		CUSTOMER DRAWING	SCALE	
MATERIAL SEE CALLOUTS		—	4:1	
SEE CALLOUTS		—	SHEET 1 OF 1	
		—	REV T	