



SPECIFICATIONS:

1. MATERIAL:
 - (1). SCREW: STEEL.
 - (2). BODY: NYLON 66 (PA 66).
 - (3). TERMINAL: PHOSPHOR BRONZE
 - (4). CAGE (*): BRASS
 - (5). COVER: NYLON 66 (PA 66).
2. PRODUCT SPECIFICATION: PS-39500-001.
3. WIRE RANGE: 30 - 16AWG.
4. TORQUE: 2 in-lbs.
5. WIRE STRIP LENGTH: 6.50/.256.
6. NUMBER OF CIRCUIT POSITIONS AVAILABLE = 2 THROUGH 20.
7. ASSEMBLY IS ROHS COMPLIANT BY EXEMPTION.
COMPONENTS MARKED WITH AN ASTERISK (*) ARE ROHS COMPLIANT BY EXEMPTION, ALL OTHERS ARE ROHS COMPLIANT.

TOLERANCES			
MM	TOL	INCH	TOL
0-6	±0.25	0-.24	±.010
>6-30	±0.40	.24-1.18	±.016
>30-120	±0.50	1.18-4.76	±.020
>120	±0.80	>4.76	±.031

REVISED DOC TOL EC NO: IPG2017-0881 DRAWN: V BASUTHKARP 2017/03/22 CHKD: APPR: BRUPERT 2017/04/18 C2	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION 		
				mm	INCH	DRAWN BY LROTHAUS	DATE 12/06/05	TITLE 3.50MM, EURO TERM BLOCK RIGHT ANGLE, PLUG			
			4 PLACES	± ---	± ---	CHECKED BY C. YORK	DATE 01/06/06				
			3 PLACES	± ---	± ---	APPROVED BY J. PAWLICKI	DATE 01/10/06	MOLEX INCORPORATED 			
			2 PLACES	± ---	± ---	MATERIAL NO.	DOCUMENT NO.				
			1 PLACE	± ---	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 2		SD-39500-001	

