


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE31310053	2012/12/04	Kevin Wang	Modify the design and Note
C	LEN1380166-168	2013/08/16	Tom_gu	Change To UA-30BFMM-SL7BXX



UA-30BFMM-SL7BXX
 XX : 01-03Meters
 01 : 01Meter
 03 : 03Meters
 Cable Length(L): 01-03Meters

Braid	編織	Shield	
Orange 28AWG	橙	9	Twist
Purple 28AWG	紫	8	
Drain 28AWG		7	Twist
Yellow 28AWG	黃	6	
Blue 28AWG	藍	5	Twist
Drain 28AWG		4	
Black 28AWG	黑	3	Twist
Green 28AWG	綠	2	
White 28AWG	白	1	Twist
Red 28AWG	紅	1	
Wire Color		Conn.	



- Note:
- ① Important Dimension.
 - Waterproof Rate: IP67
 - Connector: USB3.0-A Male Solder, Black
 - Gasket: EPDM, Black
 - Cable: USB 3.0, (1P*28#+D+Al/My)*2+1P*28#+2C*28#+F+Al+B, Black, PVC Jacket, UV Resistant, OD=5.5mm
 - Cable Length Tolerance: 01M:±40mm, 02M-03M:±60mm
 - All of Drain twisted together.

UNIT: mm	TOLERANCE ±0.5	TITLE USB 3.0, Cable Screw F Conn M Pin	Amphenol LTW 安費諾亮泰企業股份有限公司	REV. NO. UA-30BFMM-SL7BXX	CUSTOMER ALTW	DATE 2013/08/16	DATE 2013/08/16	DATE 2013/08/16
----------	----------------	---	-------------------------------	---------------------------	---------------	-----------------	-----------------	-----------------

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF AMPHENOL LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY AMPHENOL LTW.