






REVISION				
REV	DESCRIPTION	BY	DATE	CHANGE NO.
C	DRAWING UPDATED WITH EATON TEMPLATE	EDK	04/01/2017	BUEI4519

MODEL VERSION: 01	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN MILLIMETERS.		TITLE HIGH SPEED FUSES DIN 3					 Powering Business Worldwide	
	TOLERANCES UNLESS OTHERWISE SPECIFIED: GENERAL ± 0.2mm ANGULAR ± 1°								
	UNCONTROLLED COPY		DRAWN BY: JVM	DATE: 08/05/2010	SCALE: NTS	ANGLE: FIRST	SIZE: A3		
	THIS DRAWING IS CONFIDENTIAL AND THE COPYRIGHT OF EATON AND MUST NOT BE COPIED OR PASSED ON TO A THIRD PARTY WITHOUT WRITTEN CONSENT		MATERIAL: VARIOUS		FINISH: NONE		EATON Burton-on-the-Wolds, Leics, LE12 5TH Tel +44 1509 882 600		
DWG NO: 171X0016									
MODEL SOURCE FILE: U1324							REV: C	SHEET: 1 OF 1	

Part Number	Description	IN [A]	Un [V]	Art	Protection Class	Type & Size	PreArc [I^2s]	Clear [I^2s]	Loss [W]	Drawing Pos
170M8650	FUSE 1000A 1000V DIN 3 AR UR	1000	1000	IEC	AR	DIN 3	340000	2050000	150	POS-01