



M-5334

3



NOTES:

1. ALL DIMENSIONS TO BE IN INCHES.
[mm]
2. WIRE CAPACITY #6AWG TO #2AWG, SOLID OR STRANDED COPPER WIRE ONLY.



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
INSULATORS	DUREZ	BLACK
COVER	.062 STEEL	ZINC PL.
CONTACT SPRINGS	.040 COPPER	
GROUNDING SPRING	.031 PHOS. BRZ.	
GROUND CLAMP	.050 C.R.S.	ZINC PL.
CLAMPS	ALUM.	
CLAMP SCREWS	STEEL	ZINC PL.
CENTER POST	STEEL	ZINC PL.
AUX. SPRING	.020 BRONZE	
COIL SPRING	.055 ST. WIRE	COPPER PL.
FLANGE	.078 C.R.S.	BLUE

3	ADDED NOTES 1 & 2: HBL26521 WAS 26521: CONVERTED ALL DIMS. TO DECIMAL & METRIC PER DCN 11902 RCM	JPP	1/21/05
2	REMOVED WHITE FINISH FROM CLAMPS	ajc	2-8-90
1	CAT. NO. WAS FE 12971		6-8-76
SYM	REVISIONS	APP	DATE

TITLE

60A 600VAC, 4 POLE, 5 WIRE
GROUNDING HUBBELLOCK
FLANGED OUTLET

TOLERANCES UNLESS
OTHERWISE SPECIFIED
FRACTIONS $\pm 1/64$
DECIMALS $\pm .005$
ANGLES $\pm 2^\circ$

HARVEY HUBBELL, INC.

BRIDGEPORT, CONN.

DR. BY A.J.L. APP. BY
TR BY SCALE FULL
CHK'D BY DATE 6-14-71