

5

4

3

2

1

D

D

C

C

B

B

A

A



Description: CAT6 molded & booted patch cable  
 Part No: 73-889X-XXX  
 Application: Patch cable  
 Crimp Tool: N/A  
 Impedance: N/A  
 Frequency Range: N/A  
 Material: Plug RJ-45, Gold plated on contacts  
 Hood PVC  
 Cable UTP, 24 AWG, 4 twisted pairs with PE divider, stranded bare copper, UL ETL  
 EIA/TIA-568A verified category 6  
 RoHS Compliance: Yes  
 Technical Detail: N/A


DRAWING NO. 73-889X-XXX-CUST	
<b>REVISIONS</b>	
01	OFFICIAL RELEASE
	06-11-10 J J J T H
02	CHANGE VIEW
	03-29-11 J J J D <small>ECO-11-0058</small>

TABLE 1

PART NUMBER	LENGTH (FEET)	DESCRIPTION
73-889X-1	1	CAT6 MOLDED & BOOTED PATCH CABLE, 1FT
73-889X-3	3	CAT6 MOLDED & BOOTED PATCH CABLE, 3FT
73-889X-5	5	CAT6 MOLDED & BOOTED PATCH CABLE, 5FT
73-889X-7	7	CAT6 MOLDED & BOOTED PATCH CABLE, 7FT
73-889X-10	10	CAT6 MOLDED & BOOTED PATCH CABLE, 10FT
73-889X-14	14	CAT6 MOLDED & BOOTED PATCH CABLE, 14FT
73-889X-25	25	CAT6 MOLDED & BOOTED PATCH CABLE, 25FT
73-889X-50	50	CAT6 MOLDED & BOOTED PATCH CABLE, 50FT
73-889X-100	100	CAT6 MOLDED & BOOTED PATCH CABLE, 100FT

X=COLOR  
 0-GRAY  
 1-BLACK  
 2-BLUE  
 3-GREEN  
 4-RED  
 5-YELLOW  
 6-WHITE  
 7-ORANGE  
 8-PINK  
 9-PURPLE

<b>受控 CONTROLLED DOCUMENT</b>					
编号 P/N	73-889X-XXX-CUST	版本 Rev	02	日期 Rel'd Date	Jul11,11



PIN ASSIGNMENT		
	RJ-45 PLUG	RJ-45 PLUG
WHITE/ORANGE	1	1
ORANGE	2	2
WHITE/GREEN	3	3
GREEN	6	6
BLUE	4	4
WHITE/BLUE	5	5
WHITE/BROWN	7	7
BRCWN	8	8

**DIM OUTLINE**

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS	mm	JEAN.JIN	03-29-11
X	± 0.5	CHECKED BY	DATE
X.X	± 0.3	JEAN.JIN	03-29-11
X.XX	± 0.15	APPROVED BY	DATE
ANGLES	± 0.5°	DONALD	03-29-11
		U/M	mm



TITLE  
 CAT6 MOLDED & BOOTED PATCH CABLE

SHEET	DRAWING NO.	SIZE
1 OF 1	73-889X-XXX-CUST	A

THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.

5

4

3

2

1