

5

4

3

2

1

DRAWING NO.

27-9014-CUST

REVISIONS

01

OFFICIAL RELEASE

10-21-09

Y U M

2008.12.11 10:35:40

09/00

Betty

Description: BNC 2PC Crimp Jack RG-58

Part No: 27-9014

Application: For RG58Cable

Crimp Tool: 24-9958P

Impedance: 50 Ohm

Frequency Range: 0-4 GHz

Material: Body Brass Nickel plated

Contact Phos-Bronze Gold plated

Insulator PE


Crimp Sleeve Brass Nickel plated

RoHS Compliance: Yes

Technical Detail: Refer to Emerson Document P/N 27-0000

受控 CONTROLLED DOCUMENT

编号 P/N	27-9014	版本 Rev	01	日期 Rel'd Date	DEC 17,09
-----------	---------	-----------	----	------------------	-----------

DIM OUTLINE

CUSTOMER COPY

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS		BETTY.YU	10-21-09
X	± 0.5	CHECKED BY	DATE
X.X	± 0.3	BETTY.YU	10-21-09
X.XX	± 0.1	APPROVED BY	DATE
ANGLES	± 0.5°	THOMAS	10-21-09
		U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

 EMERSON Network Power		Connectivity Solutions	
TITLE			
BNC 2PC CRIMP JACK RG-58			
SHEET	DRAWING NO.	SIZE	
1 OF 1	27-9014-CUST	A	